

Product sheet



LEGRAND

Remote trip head isolating switch DX-IS - visible load break - 3P 400 V~ - 63 A

REF. 406536 | EAN. 3245064065368

> [Visit e-catalogue](#)

Product characteristics

- Isolating switches DX³ - IS - from 16 A to 125 A - Double break contacts
- Remote trip head isolating switches - Red handle - AC 22 A, AC 23 A - Visible contact indication - Remote tripping with associated control auxiliary - Can be fitted with motorised controls and 2 DX³ signalling auxiliaries - Visual indication of the actual status of the contacts : - Closed position (red indicator) - Open position (green indicator) 3P - 400 V~ - Compatible with prong - type and fork type supply busbars - Nominal rating In = 63 A - Number of modules : 3

Documentation

TECHNICAL DOCUMENTATION

 F01677EN-01.pdf | PDF (0.57Mo)

 F01677FR-02.pdf | PDF (0.5Mo)

CAD & Design specs / BIM

 406535.dwg | DWG (0.2Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0058.pdf | PDF (0.09Mo)

 ex223001_0060.pdf | PDF (0.04Mo)

Agreements & Certificates

 OC / CB-632428C | (0.25Mo)

 OC / CB-FR_718581 | (0.33Mo)

 LGRP-00689-V01.01-EN.pdf | PDF (0.56Mo)

 NF App Domestic-NF208_1039/A1 | (0.52Mo)