

Product sheet



LEGRAND

RCD RX³ - 2P 230 V~ - 40 A - 100 mA - AC type

REF. 402029 | EAN. 3245064020299

> [Visit e-catalogue](#)

Product characteristics

- RCCBs RX³ - residual current circuit breakers from 25 A to 63 A - AC and A types - Conform to IEC 61008 - 1 - AC type : detect AC component faults - A type : detect AC and DC component faults - Compatible with prong - type and fork type supply busbars - Do not accept auxiliaries
- 2-pole - 230 V~AC type - Sensitivity : 100 mA - In : 40 A - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

 F01535EN-04.pdf | PDF (0.94Mo)

CAD & Design specs / BIM

 402038.dwg | DWG (0.13Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0052.pdf | PDF (0.11Mo)

Agreements & Certificates

 LGRP-02039-V01.01-EN.pdf | PDF (0.76Mo)

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)

 OC / CB-CB FR_713498/M1 | (2.3Mo)

 VDE-40034493 | (0.38Mo)