

# Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - double pole switch with blue led power indicator - 45A - Brushed Stainless Steel

REF. 832023 | EAN. 3414970660565

> [Visit e-catalogue](#)

## Product characteristics

- 45A, 250V~
- Screw terminals accept wires up to 16mm<sup>2</sup>
- Flush mounting back box to be minimum 35mm deep
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

### Usage

- Complies to British Standards certifications for heavy loads

### Advantages

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation


### TECHNICAL DOCUMENTATION

 F02258EN-00.pdf | PDF (0.63Mo)

### Agreements & Certificates

 OC / CB-FR\_708126 | (0.6Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0728.pdf | PDF (0.08Mo)