

Product sheet



LEGRAND

RCD LR - 4P 400 V~ - 63 A - 30 mA - A type

REF. 402076 | EAN. 3245064020763

> [Visit e-catalogue](#)

Product characteristics

- RCCBs RX³ - residual current circuit breakers from 25 A to 63 A - AC and A types - Conform to IEC 61008 - 1 - AC type : detect AC component faults - A type : detect AC and DC component faults - Compatible with prong - type and fork type supply busbars - Do not accept auxiliaries
- 4-pole - 400 V~ neutral on right - hand sideA type - Sensitivity : 30 mA - In : 63 A - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

 F01536EN-02.pdf | PDF (0.96Mo)

CAD & Design specs / BIM

 402076.dwg | DWG (0.13Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0052.pdf | PDF (0.11Mo)

Agreements & Certificates

 LGRP-02039-V01.01-EN.pdf | PDF (0.76Mo)

 LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)

 VDE-40034495 | (0.37Mo)

 OC / CB-CB FR_705078/M1 | (3.33Mo)

 LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)