

# Product sheet



SYNERGY™ LEGRAND

Synergy™ Sleek - Double Pole switch with blue led power indicator -20A - Glossy Gold

REF. 832412 | EAN. 3414970662927

> [Visit e-catalogue](#)

## Product characteristics

- 20AX, 250V~
- Screw type terminals, which accept wires up to 6mm<sup>2</sup> or 2 x 4mm<sup>2</sup>.
- Large angled easy - to - access cable entries and terminals marked for easy identification.
- Screwless cover plate is square 86x86 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

## Recommendation / Restriction

- Recommended inside use only

## The product's benefits

### Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

### Advantages

- Plate and switch rocker are made in the same Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

## Documentation

### TECHNICAL DOCUMENTATION

 F02257EN-01.pdf | PDF (0.75Mo)

### Agreements & Certificates

 OC / CB-FR\_708093 | (0.72Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0728.pdf | PDF (0.08Mo)