

Product sheet



LEGRAND

MCB - DX³ - 16 kA - direct current - 12 V= to 500 V= - 2P - 25 A

REF. 409570 | EAN. 3245064095709

> [Visit e-catalogue](#)

Product characteristics

- MCBs DX³ - 16 kA - direct current - thermal magnetic circuit breakers from 0,5 A to 63 A - Operating voltage from 12 V to 500 V - Breaking capacity - 16 kA - IEC 60947 - 2 - 250 V - 10 kA - IEC 60947 - 2 - 440 V - 6 kA - IEC 60947 - 2 - 500 V - Magnetic threshold from 5 to 7 I_n - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- Direct current circuit breakers - Nominal rating I_n : 25 A - Number of poles protected : 2 - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION



F01462EN-02.pdf | PDF (0.37Mo)



F01462FR-02.pdf | PDF (0.4Mo)

CATALOGUE PAGE & OTHERS



ex223001_0069.pdf | PDF (0.11Mo)



ex223001_0076-0077.pdf | PDF (0.2Mo)