


Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 3 gang 2-way switch - 20AX - Brushed Stainless Steel

REF. 833133 | EAN. 3414970665669

> [Visit e-catalogue](#)

Product characteristics

- 20AX, 250V~
- Screw type terminals, marked for easy identification
- Large angled easy - to - access cable entries and captive screws
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Can be used as a simple switch but can also be associated with another two-way switch, thus allowing to turn the light on and off from two different control points.

Advantages

- Plate and rockers in same metal: austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes


Documentation

TECHNICAL DOCUMENTATION

 F02251EN-01.pdf | PDF (0.23Mo)

Agreements & Certificates

 ASTA-782 | (0.27Mo)

 OC / CB-FR_708093 | (0.72Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0722.pdf | PDF (0.09Mo)