

Product sheet



DX³ LEGRAND

RCBO - DX³ 6000 -10 kA -4P-400 V~ -16 A -30 mA -A type

REF. 411234 | EAN. 3245064112345

> [Visit e-catalogue](#)

Product characteristics

- RCBOs DX³ 6000 - 10 kA - residual current circuit breakers from 10 A to 63 A - AC, A and F types - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping - Breaking capacity : - 6000 - IEC 61009 - 1 - 10 kA / IEC 60947 - 2 for single pole + neutral, 2 and 4-pole - AC type : detect AC component faults - A type : detect AC and DC component faults - F type (High immunity) : detect AC and pulsating DC residual currents. Enhanced immunity to unwanted tripping in disturbed environments. Detection of high frequency fault currents - Can be equipped with DX³ signalling and remote tripping auxiliaries and motorised controls
- 4-pole - 400 V~ - 4 - module RCBOs are compatible with prong - type and fork type supply busbars - 7 - module RCBOs are compatible with prong - type supply busbars only A Type 30 mA - C curve - Nominal rating In : 16 A - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

-  F01315FR-07.pdf | PDF (2.6Mo)
-  F01315EN-08.pdf | PDF (2.56Mo)
-  LE04155AB.pdf | PDF (8.3Mo)

CAD & Design specs / BIM

-  411189.dwg | DWG (0.17Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0076-0077.pdf | PDF (0.2Mo)
-  ex223001_0063.pdf | PDF (0.11Mo)

Agreements & Certificates

-  NF App Domestic-NF012_4280 | (0.77Mo)
-  AENOR-030/002274 | (0.56Mo)
-  OC / CB-CB FR_718648 | (1.67Mo)
-  LGRP-00796-V01.01-EN.pdf | PDF (0.57Mo)
-  VDE-40042544 | (0.26Mo)