

Product sheet



EMDX³ LEGRAND

EMDX3 energy meter mono direct 63A 230V 2tariff RS485

REF. 412081 | EAN. 3414971413818

> [Visit e-catalogue](#)

Product characteristics

- Direct connection up to 63A 1P.
- Communication : Modbus RS 485.
- Double tariff or Pulse input to collect other meter (gas, water, electrical meters).
- No MID version.
- Bidirectional measure of production and consumption energies.

The product's benefits

Installation

- Simple installation by direct connection up to 63A without the use of a current transformer. Limited location due to its compact size of 2 modules. Easy connection of communication thanks to removable connectors. One input connector for double tariff or Pulse input to collect water or gas meters without using added concentrator device.

Usage

- Backlit display and simple access to easy reading of data. Pre-visualization of parameters. Settings mode protected by user code Bidirectional measure of production and consumption energies

Advantages

- Measure of run hours on each tariff.

Documentation

TECHNICAL DOCUMENTATION

-  IDP000201_F02835EN_05.pdf | PDF (5.36Mo)
-  F02835EN_01.pdf | PDF (5.36Mo)
-  LE11306BA.pdf | PDF (1.55Mo)
-  IDP000201_F02835FR_05.pdf | PDF (4.97Mo)
-  F02835FR_02.pdf | PDF (2.07Mo)
-  → LE11306BB_01.pdf | PDF (1.35Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0120.pdf | PDF (0.06Mo)
-  ex223001_0118.pdf | PDF (0.12Mo)

 PR_412081.pdf | PDF (0.26Mo)

 LE11305BD.pdf | PDF (1.77Mo)

 Guide Technique : EMDX³ compteurs d'énergie | PDF (3.04Mo)

 Technical Guide: EMDX³ electricity meters | PDF (3.04Mo)

CAD & Design specs / BIM

 412082.dwg | DWG (0.1Mo)