

# Product sheet



## LEGRAND

SPD - T2 - I<sub>max</sub> 40 kA/pole - 440 V~ (IT) - 4P

REF. 412233 | EAN. 3414970517586

> [Visit e-catalogue](#)

## Product characteristics

- Class II (T2) low voltage SPDs - Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643 - 11 standards - Recommended for distribution boards
- T2 SPDs - SPDs with plug-in modules and status indicators : - Green : SPD operational - Orange : plug-in modules to be replaced
- T2 - I<sub>max</sub> 40 kA/pole - 440V~ (IT) - SPDs recommended for big installations - Up : 2.1 kV - I<sub>n</sub> = 20 kA/pole - U<sub>c</sub> : 440 V~ - Earthing systems : TT, TNC, TNS, IT - Recommended MCB : DX<sup>3</sup> 25 A - C curve - Number of poles : 4P - Remote status monitoring (FS contact) : Yes - Number of modules : 4

## Documentation

### TECHNICAL DOCUMENTATION

- F02060EN\_05.pdf | PDF (0.62Mo)
- F02060FR\_06.pdf | PDF (0.61Mo)
- Technical Guide: Surge Protective Devices | PDF (8.37Mo)
- LE07561AA\_6.pdf | PDF (0.53Mo)

### CAD & Design specs / BIM

- 412233.dwg | DWG (0.37Mo)

### CATALOGUE PAGE & OTHERS

- ex223001\_0088-0089.pdf | PDF (0.16Mo)
- ex223001\_0087.pdf | PDF (0.12Mo)
- ex223001\_0085.pdf | PDF (0.07Mo)

### Agreements & Certificates

- LGRP-2015-068-V1-EN.pdf | PDF (0.62Mo)
- OC / CB-AT 4283 | (0.27Mo)