

Product sheet



LEGRAND

SPD with ICC protection 25KA t2 imAX 40KA 1P+N left with fault signalling

REF. 412214 | EAN. 3414971552913

> [Visit e-catalogue](#)

Product characteristics

- Surge 3P+N : L - N and N - PE protection modes (common and differential modes), the N pole being protected by encapsulated spark gaps. Also called 3+1
- T2 add - on SPDs
- Recommended MCB : DX³ 20A - C curve

The product's benefits

Installation

- Recommended for distribution boards

Usage

- SPDs recommended for small installations

Documentation

TECHNICAL DOCUMENTATION

- [LE11368AA_3.pdf](#) | PDF (1.09Mo)
- [EXB20026_TG_Surge_Protective_Devices_EN.pdf](#) | PDF (8.37Mo)
- [F02952FR_01.pdf](#) | PDF (0.77Mo)
- [F02952EN_01.pdf](#) | PDF (0.77Mo)

CAD & Design specs / BIM

- [412210.dwg](#) | DWG (0.22Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0088-0089.pdf](#) | PDF (0.16Mo)
- [ex223001_0087.pdf](#) | PDF (0.12Mo)
- [ex223001_0085.pdf](#) | PDF (0.07Mo)