

Product sheet



LEGRAND

RCCB TX³ - 2P 230 V~ - 300 mA - 63 A - AC type

REF. 411531 | EAN. 3414970352620

> [Visit e-catalogue](#)

Product characteristics

- RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types - Conform to IEC 61008 - 1 - Compatible with prong - type and fork type supply busbars - AC type : detect AC component faults - A type : detect AC and DC component faults
- 2-pole - 230 V~AC type - Sensitivity : 300 mA - In : 63 A - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION



F01575EN-03.pdf | PDF (0.78Mo)

CAD & Design specs / BIM



411910.dwg | DWG (0.15Mo)

CATALOGUE PAGE & OTHERS



ex223001_0056.pdf | PDF (0.12Mo)

Agreements & Certificates



LGRP-02039-V01.01-EN.pdf | PDF (0.76Mo)



VDE-40041193 | (0.46Mo)



OC / CB-CB FR_713498/M1 | (2.3Mo)