

Product sheet



LEGRAND

RCCB TX³ - 4P 400 V~ - 100 mA - 80 A - AC type

REF. 411720 | EAN. 3414970352200

> [Visit e-catalogue](#)

Product characteristics

- RCCBs TX³ residual current circuit breakers - from 16 A to 80 A - AC and A types - Conform to IEC 61008 - 1 - Compatible with prong - type and fork type supply busbars - AC type : detect AC component faults - A type : detect AC and DC component faults
- 4-pole 400 V~ - Neutral on right - hand side AC type - Sensitivity : 100 mA - In : 80 A - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION



F01576EN-03.pdf | PDF (0.7Mo)

CAD & Design specs / BIM



411709.dwg | DWG (0.17Mo)

CATALOGUE PAGE & OTHERS



ex223001_0056.pdf | PDF (0.12Mo)

Agreements & Certificates



LGRP-02039-V01.01-EN.pdf | PDF (0.76Mo)



LGRP-00366-V02.01-FR.pdf | PDF (0.6Mo)



VDE-40041193 | (0.46Mo)



OC / CB-CB FR_705078/M1 | (3.33Mo)



LGRP-00366-V02.01-EN.pdf | PDF (0.64Mo)