

Product sheet



SYNERGY™ LEGRAND

Synergy™ Authentic - Double Pole switch with blue led power indicator -20A - Glossy Gold

REF. 833412 | EAN. 3414970667885

> [Visit e-catalogue](#)

Product characteristics

- 20AX, 250V~
- Screw type terminals, which accept wires up to 6mm² or 2 x 4mm².
- Large angled easy - to - access cable entries and terminals marked for easy identification.
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Advantages

- Plate and switch rocker in same metal: Stainless steel rust resistance
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes


Documentation

TECHNICAL DOCUMENTATION

 F02252EN-01.pdf | PDF (0.77Mo)

Agreements & Certificates

 ASTA-782 | (0.27Mo)

 OC / CB-FR_708093 | (0.72Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0723.pdf | PDF (0.11Mo)