

# Product sheet



## CX<sup>3</sup> LEGRAND

Contactor CX<sup>3</sup> with front face handle 4 pole - 40A - 400V~ - 4 NO contacts with 24V~ coil - 3 modules

REF. 412518 | EAN. 3245064125185

> [Visit e-catalogue](#)

## Product characteristics

- Utilization category : AC7a or AC1 - 40A / AC7b or AC3 - 22A
- Can be equipped with auxiliaries reference 412431
- Conform to IEC/EN 61095
- 24V~ coil

## Recommendation / Restriction

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

## The product's benefits

### Installation

- Easy integration: fitted with two DIN rail clamps, one top side and one bottom side to ease the clipping. Allows the insertion of prong busbar at the top side.

### Usage

- Equipped with a front face handle to get the possibility to also control it on-site directly on the device itself (test and repair function). Permanent ON or OFF without automatic reset. Also Fitted with a label holder allowing a clear, visible and convenient identification of the circuit.

## Documentation

### TECHNICAL DOCUMENTATION

 F01333FR-02.pdf | PDF (0.17Mo)

 F01333EN-02.pdf | PDF (0.17Mo)

### CAD & Design specs / BIM


 412518.dwg | DWG (0.15Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_0093.pdf | PDF (0.28Mo)

 ex223001\_0095.pdf | PDF (0.05Mo)

### Agreements & Certificates

 VDE-40034227 | (0.4Mo)

 NF App Domestic-NF012\_3114 | (0.55Mo)

 OC / CB-FR\_712933 | (0.41Mo)

