

Product sheet



SYNERGY™ LEGRAND

Synergy Authentic 1gang double pole switch - 45A - Glossy gold

REF. 833422 | EAN. 3414970667960

> [Visit e-catalogue](#)

Product characteristics

- 45A, 250V~
- Screw terminals accept wires up to 16mm²
- Flush mounting back box to be minimum 35mm deep
- Cover plate is square 86x86 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Recommendation / Restriction

- Recommended inside use only

The product's benefits

Installation

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Usage

- Complies to British Standards certifications for heavy loads

Advantages

- Plate in Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Documentation

TECHNICAL DOCUMENTATION



F02253EN-00.pdf | PDF (0.73Mo)

Agreements & Certificates



OC / CB-FR_708126 | (0.6Mo)



ASTA-783 | (0.26Mo)

CATALOGUE PAGE & OTHERS



ex223001_0723.pdf | PDF (0.11Mo)