

Product sheet



CTX³ LEGRAND

Auxiliary contact 2NO2NC for CTX3 3P 9A to 150A and 4P 40A to 135A - front mounting

REF. 416855 | EAN. 3414970408488

> [Visit e-catalogue](#)

Product characteristics


- 2NO + 2NC Auxiliary contact unit (Ith = 16A) NC auxiliary contact meets the definition of mirror contact according to IEC 60947 - 4 - 1 standard
- Screw terminals capacity : 2 x 1mm² to 2,5mm²
- Mounting on the front of CTX3 3P from 9A to 150A and 4P from 40A to 135A
- Minimum switching voltage: 24V DC Minimum switching current: 10mA
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Read the instructions before installing this product.

Documentation

TECHNICAL DOCUMENTATION

 [EXB19046_TG_3phase-asynchronous-motors_EN.pdf](#) | PDF (6.11Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0287.pdf](#) | PDF (0.05Mo)

 [ex223001_0286.pdf](#) | PDF (0.11Mo)

 [ex223001_0288-0289.pdf](#) | PDF (0.1Mo)

The product's benefits

Installation

- Fixing on the front side of the contactor