

Product sheet



LEGRAND

Active power compensator

REF. 040149 | EAN. 3414970856227

> [Visit e-catalogue](#)

Product characteristics

- Mosaic Programm e mechanisms - motion and presence sensors - All sensors are compatible with any lamp - Detection field : 120° - Detection range : 8 m - Recomm ended installation height : 1.20 m - Integrated self - protection against overloads and short - circuits. - 2 modules
- Active Power Compensator - Makes 2 - wire electronic lighting control units without neutral compatible with all comm ercially - available loads (LED, compact fluorescent, ELV halogen with ferromagnetic or electronic ballast, 230 V halogen, fluorescent tube, incandescent) - Consumption 0,4 W

Documentation

TECHNICAL DOCUMENTATION

- [LE09710AB.pdf](#) | PDF (0.08Mo)
-  [F02436FR-02.pdf](#) | PDF (0.17Mo)
-  [F02436EN-02.pdf](#) | PDF (0.17Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0743.pdf](#) | PDF (0.15Mo)
-  [ex223001_0562.pdf](#) | PDF (0.08Mo)
-  [ex223001_0671.pdf](#) | PDF (0.05Mo)
-  [ex223001_1176.pdf](#) | PDF (0.07Mo)
-  [ex223001_0679.pdf](#) | PDF (0.08Mo)
-  [ex223001_0663.pdf](#) | PDF (0.07Mo)
-  [ex223001_0727.pdf](#) | PDF (0.08Mo)
-  [ex223001_0693.pdf](#) | PDF (0.07Mo)
-  [ex223001_1177.pdf](#) | PDF (0.07Mo)
-  [ex223001_0564.pdf](#) | PDF (0.06Mo)
-  [ex223001_0793.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

-  [LGRP-01679-V01.01-FR.pdf](#) | PDF (0.85Mo)