

Product sheet



CTX³ LEGRAND

Contactor CTX3 mini 3P 6A 1NO 24V AC

REF. 417000 | EAN. 3414970403810

> [Visit e-catalogue](#)

Product characteristics





- Rating 6A (AC - 3) for the switching of 3 - ph motors up to 2,2 kW (415V). Resistive loads up to 20A (AC - 1).
- Screw terminals capacity : Power 2 x 1,25mm² to 2mm² / Coil 0,75mm² to 2,5mm² / Aux. Circuit 0,75mm² to 2,5mm²
- 1NO auxiliary contact. Can be equipped with all Legrand CTX3 mini auxiliaries and Accessories .
- Endurance: up to 12 million mechanical operations and 1 million electrical operations. Number of operation cycles (AC-3) per hour : 1800.
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Recommended for the switching of inductive and non-inductive loads. Read the instructions before installing this product. Use only Legrand branded accessories.

Documentation

TECHNICAL DOCUMENTATION

-  F02017FR-05 .pdf | PDF (0.63Mo)
-  LE07420AB.pdf | PDF (4.77Mo)
-  F02017EN-05.pdf | PDF (0.66Mo)
-  EXB19046_TG_3phase-asynchronous-motors_EN.pdf | PDF (6.11Mo)

CAD & Design specs / BIM



-  417000.dwg | DWG (0.16Mo)

The product's benefits

Installation

- Possible fixing on 35 mm "top hat" mounting rail (IEC 60715) and on mounting plate. Reduced size to optimize the space available in the cabinet.

CATALOGUE PAGE & OTHERS

-  ex223001_0280.pdf | PDF (0.09Mo)
-  ex223001_0281.pdf | PDF (0.07Mo)