

Product sheet



CTX³ LEGRAND

Control relay CTX3 2NO2NC 24V AC

REF. 416820 | EAN. 3414970407726

> [Visit e-catalogue](#)

Product characteristics

- 2NO + 2NC main contacts
- Screw terminals capacity : Power 2 x 1,25mm² to 2mm² / Coil 0,75mm² to 2,5mm²
- Contacts number can be extended with CTX3 mini auxiliary contacts blocks.
- Endurance: up to 20 million mechanical operations and 0,5 million electrical operations (AC-15). Number of operation cycles (AC-3) per hour : 1800.
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Read the instructions before installing this product.

Documentation

TECHNICAL DOCUMENTATION

 F02019FR-01.pdf | PDF (0.6Mo)

 LE07420AB.pdf | PDF (4.77Mo)

 F02019EN-01.pdf | PDF (0.63Mo)

 Technical Guide: Protection and control of 3-phase asynchronous motors | PDF (6.11Mo)

CAD & Design specs / BIM

 416800.dwg | DWG (0.14Mo)

The product's benefits

Installation

- Possible fixing on 35 mm "top hat" mounting rail (IEC 60715) and on mounting plate. Reduced size to optimize the space available in the cabinet.

CATALOGUE PAGE & OTHERS

 ex223001_0287.pdf | PDF (0.05Mo)