

Product sheet



LEGRAND

Energy Web Server for remote consultation for 32 MODBUS addresses or 32 pulse counters

REF. 414948 | EAN. 3414970805560

> [Visit e-catalogue](#)

Product characteristics

- Power supervision system - remote control, monitoring and measurement - With the Legrand Power supervision system, circuit breakers are integrated in a supervision system - You can therefore check the status of the circuit breakers, measure the electrical values and control the circuit breakers remotely - MODBUS protocol
- Energy management multi-support web servers - Allow remote configuration, test, control and visualization, via a web browser on PCs, smartphones, web viewers, tablet computers, of data collected from : protection devices (DX³ add - on modules with integrated measurement control unit, DPX³ and DMX³) , EMDX³ electricity meters and multi-function measuring units, CX³ energy management system and Green'up charging stations for electric vehicles Rail mounting - Direct IP connection - Power supply : 9 to 28 V= with the help of a single-phase switching mode power supply Cat.No 1 467 21 to be ordered separately - For 32 Modbus adresses or 32 pulse modules - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

-  F02466EN-03.pdf | PDF (0.37Mo)
-  F02466FR-03.pdf | PDF (0.38Mo)
-  USER MANUAL-RA00254AA_EN.pdf | PDF (25.3Mo)
-  LE10102AB.pdf | PDF (0.47Mo)

CAD & Design specs / BIM

-  414947.dwg | DWG (0.12Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0518.pdf | PDF (0.06Mo)
-  ex223001_0117.pdf | PDF (0.07Mo)

Software & configurators

-  Energy_Manager_Web_Server_414947_48_49_3_14_1.zip | ZIP (33.46Mo)