

Product sheet



MPX³ LEGRAND

Motor protection circuit breaker MPX3 32S 0.16-0.25A
100kA

REF. 417301 | EAN. 3414970395054

> [Visit e-catalogue](#)

Product characteristics

- For the protection of 3 - ph motors 0,06kW / 415V
- Icu = 100kA / 415V Ics = 100kA / 415V
- Screw terminals capacity : 1mm² to 10mm² / 2 x 1mm² to 6mm²
- Compatible with MPX3 auxiliaries
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Recommended for the protection of 3-ph motors 0,06kW / 415V. Read the instructions before installing this product. Use only Legrand branded accessories.

The product's benefits

Installation

- Possible fixing on 35 mm "top hat" mounting rail (IEC 60715). Reduced size to optimize the space available in the cabinet.

Usage

- Easy operation thanks to the rocker switch

Documentation

TECHNICAL DOCUMENTATION

 F01988FR-05.pdf | PDF (2.88Mo)

 LE07207AB.pdf | PDF (4.25Mo)

 F01988EN-05.pdf | PDF (2.86Mo)

 Technical Guide: Protection and control of 3-phase asynchronous motors | PDF (6.11Mo)

CAD & Design specs / BIM

 417300.dwg | DWG (0.15Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0270.pdf | PDF (0.09Mo)

 ex223001_0272-0273.pdf | PDF (0.18Mo)

 ex223001_0276-0277.pdf | PDF (0.69Mo)

 ex223001_0274.pdf | PDF (0.04Mo)

 ex223001_0275.pdf | PDF (0.07Mo)

Agreements & Certificates

 LGRP-00211-V01.01-EN.pdf | PDF (0.61Mo)