

Product sheet



MPX³ LEGRAND

Thermal magnetic trip signaling switch for MPX3 63/100 - side mounting

REF. 417408 | EAN. 3414970503022

> [Visit e-catalogue](#)

Product characteristics

- 1NO + 1NC Auxiliary contact unit (I_{th} = 10A at 40°C / 6A at 60°C)
- Rated supply current AC - 15 : 6A / 24V - 4A / 240V Rated supply current DC - 13 : 2A / 24V - 0,25A / 220V
- Screw terminals capacity : 2x 0,5mm² to 2,5mm²
- Compatible with MPX3 63H, MPX3 100H
- The device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Recommendation / Restriction

- Product specially designed for tertiary and industrial installations. Read the instructions before installing this product.

Documentation

TECHNICAL DOCUMENTATION

 Technical Guide: Protection and control of 3-phase asynchronous motors | PDF (6.11Mo)

The product's benefits

Installation

- Fixing on the left side of the breaker

CATALOGUE PAGE & OTHERS

 ex223001_0271.pdf | PDF (0.1Mo)