

Product sheet



DPX³ 160 LEGRAND

Sealable terminal shields for DPX3 160 circuit breaker
4 poles

REF. 422058 | EAN. 3414970378545

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 630 - S2 electronic release MCCBs from 250 to 630 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with earth leakage modules or with residual current relays - Supplied complete with : - Fixing screws - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs electronic release S2 - fixed version - Adjustment of Ir, Isd, tr, tsd - Instantaneous protection If = 5 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity - 4P version : adjustment of neutral on Front panel Breaking capacity Icu 36 kA (400 V~) - 3P - In : 400 A

Documentation

TECHNICAL DOCUMENTATION

-  ModbusTable_14.pdf | PDF (0.38Mo)
- LE07062AB.pdf | PDF (0.81Mo)
- LE07061AA-02.pdf | PDF (1.99Mo)
-  F01959FR01_DPX3_630ELE_FRAv3.pdf | PDF (1.04Mo)
-  EXB20072_logic_selectivity (print).pdf | PDF (6.63Mo)
-  EXB15015_TG_Coordination_EN.pdf | PDF (5.41Mo)
-  EXB19026_CA_DPX3_125HP250HP_630_1600EN.pdf | PDF (82.93Mo)
- LE08866AC.pdf | PDF (6.7Mo)
-  F01959N04_DPX3630_ELE.pdf | PDF (3.03Mo)
-  PRT220015_GT_selectivite_logique.pdf | PDF (6.38Mo)
-  EXB21086_CA_DPX3HP125_250_DPX3630_1600FR.pdf | PDF (83.49Mo)

CAD & Design specs / BIM

-  422060.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0199.pdf | PDF (0.04Mo)

Agreements & Certificates

-  DC-D13_13-SELECTIVITE _FILIAION-A-3-NIVEAUX.pdf | PDF (0.62Mo)
-  OC / CB-SE-91831 | (1.1Mo)

Software & configurators



PowerControlStation 5.0.74.zip | ZIP (52.52Mo)