

Product sheet



LEGRAND

MCCB DPX³ 630 - S2 elec release + central - 3P - Icu 50 kA (400 V~) - In 400 A

REF. 422108 | EAN. 3414970379047

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 630 - S2 electronic release MCCBs from 250 to 630 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with earth leakage modules or with residual current relays - Supplied complete with : - Fixing screws - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs electronic release S2 with energy metering central unit - fixed version - Adjustment of Ir, Isd, tr, tsd - Instantaneous protection If = 5 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity - 4P version : adjustment of neutral on Front panel Breaking capacity Icu 50 kA (400 V~) - 3P - In : 400 A

Documentation

TECHNICAL DOCUMENTATION

- LE07062AB.pdf | PDF (0.81Mo)
- ModbusTable_17.pdf | PDF (0.41Mo)
- LE07061AA-02.pdf | PDF (1.99Mo)
- F01959FR01_DPX3_630ELE_FRAv3.pdf | PDF (1.04Mo)
- Technical guide: Logical selectivity | PDF (6.63Mo)
- Technical Guide: Coordination between protection devices | PDF (5.41Mo)
- Workshop Book: DPX³ 125HP & 250HP - DPX³ 630 & 1600 | PDF (82.93Mo)
- F01959N05_DPX3_630_ELE.pdf | PDF (3.04Mo)
- LE08866AC.pdf | PDF (6.7Mo)
- PRT220015_GT_selectivite_logique.pdf | PDF (6.38Mo)
- Cahier d'atelier : DPX³ 125 HP et 250 HP & DPX³ 630 et 1600 | PDF (83.49Mo)

CAD & Design specs / BIM

- 422100.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0199.pdf | PDF (0.04Mo)

Software & configurators

- PowerControlStation 5.0.0.78.zip | ZIP (52.57Mo)