

Product sheet



LEGRAND

MCCB DPX³ 1600 - thermal magnetic release - 3P - Icu 70 kA (400 V~) - In 1000 A

REF. 422277 | EAN. 3414970380432

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 1600 - thermal magnetic release MCCBs from 630 to 1250 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs thermal magnetic release fixed version - Thermal adjustable from 0,8 to 1 In - Magnetic adjustable from 5 to 10 In. Breaking capacity Icu 70 kA (400 V~) - 3P - In : 1000 A

Documentation

TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
-  Workshop Book: DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.04Mo)
-  Cahier d'atelier : DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.32Mo)
-  Technical Guide: Coordination between protection devices | PDF (5.41Mo)
-  F01963EN04_DPX31600_TM.pdf | PDF (1.64Mo)

CAD & Design specs / BIM

-  422274.dwg | DWG (0.17Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0181.pdf | PDF (0.1Mo)
-  ex223001_0198.pdf | PDF (0.03Mo)
-  ex223001_0196-0197.pdf | PDF (0.52Mo)

Agreements & Certificates

-  LGRP-00819-V01.01-EN.pdf | PDF (0.64Mo)