

# Product sheet



## LEGRAND

MCCB DPX<sup>3</sup> 1600 - S2 electronic release - 4P - Icu 70 kA (400 V~) - In 800 A

REF. 422330 | EAN. 3414970380968

> [Visit e-catalogue](#)

## Product characteristics

- DPX<sup>3</sup> 1600 - S2 electronic release MCCBs from 630 to 1600 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL<sup>3</sup> cabinets and enclosures
- MCCBs electronic release S2 fixed version - Adjustment of Ir, Isd, tr, tsd - Instantaneous protection If = 20 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity Breaking capacity Icu 70 kA (400 V~) - 4P - In : 800 A

## Documentation

### TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- ModbusTable\_15.pdf | PDF (0.41Mo)
- F01964FR01\_DPX3\_1600ELE\_FRAv3.pdf | PDF (0.7Mo)
- LE08865AB.pdf | PDF (5.48Mo)
- LE07038AB.pdf | PDF (1.78Mo)
- Technical guide: Logical selectivity | PDF (6.63Mo)
- Technical Guide: Coordination between protection devices | PDF (5.41Mo)
- Workshop Book: DPX<sup>3</sup> 125HP & 250HP - DPX<sup>3</sup> 630 & 1600 | PDF (82.93Mo)
- LE08866AC.pdf | PDF (6.7Mo)
- F01964EN04\_DPX3\_1600\_ELE.pdf | PDF (2.99Mo)
- PRT220015\_GT\_selectivite\_logique.pdf | PDF (6.38Mo)
- Cahier d'atelier : DPX<sup>3</sup> 125 HP et 250 HP & DPX<sup>3</sup> 630 et 1600 | PDF (83.49Mo)

### CAD & Design specs / BIM

- 422381.dwg | DWG (0.19Mo)

### CATALOGUE PAGE & OTHERS

- ex223001\_0199.pdf | PDF (0.04Mo)

### Software & configurators

- PowerControlStation 5.0.0.78.zip | ZIP (52.57Mo)

