

Product sheet



LEGRAND

MCCB DPX³ 1600 - Sg electronic release - 3P - Icu 50 kA (400 V~) - In 1600 A

REF. 422411 | EAN. 3414970381774

> [Visit e-catalogue](#)

Product characteristics

- DPX³ 1600 - Sg electronic release MCCBs from 630 to 1600 A - Moulded case MCCBs for switching, control isolation and protection of low voltage electrical lines - Can be fitted with auxiliaries - Can be used with residual current relays - Supplied complete with : - Connection plates for bars - Insulated shields (phase barriers) - Conform to IEC 60947 - 2 - Sealable adjustment - Can be mounted on plate in XL³ cabinets and enclosures
- MCCBs electronic release Sg fixed version - Adjustment of Ir, Isd, Ig, tr, tsd, tg - Instantaneous protection If = 20 kA - Green indicator lamp - Connector for test unit - Logic and dynamic selectivity Breaking capacity Icu 50 kA (400 V~) - 3P - In : 1600 A

Documentation

TECHNICAL DOCUMENTATION

- LE07037AB.pdf | PDF (0.94Mo)
- F01964FR01_DPX3_1600ELE_FRAv3.pdf | PDF (0.7Mo)
- LE08865AB.pdf | PDF (5.48Mo)
- modbustable_20.pdf | PDF (0.41Mo)
- LE07038AB.pdf | PDF (1.78Mo)
- Technical guide: Logical selectivity | PDF (6.63Mo)
- Technical Guide: Coordination between protection devices | PDF (5.41Mo)
- Workshop Book: DPX³ 125HP & 250HP - DPX³ 630 & 1600 | PDF (82.93Mo)
- LE08866AC.pdf | PDF (6.7Mo)
- F01964EN04_DPX3_1600_ELE.pdf | PDF (2.99Mo)
- PRT220015_GT_selectivite_logique.pdf | PDF (6.38Mo)
- Cahier d'atelier : DPX³ 125 HP et 250 HP & DPX³ 630 et 1600 | PDF (83.49Mo)

CAD & Design specs / BIM

- 422411.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0199.pdf | PDF (0.04Mo)

Software & configurators

- PowerControlStation 5.0.0.78.zip | ZIP (52.57Mo)

