

Product sheet



LEGRAND

Backup function modules for stabilised switched modules power supply -max rating 40 A

REF. 146690 | EAN. 3414970543639

> [Visit e-catalogue](#)

Product charateristics

- Stabilised switched mode power supplies - additional functions - Used to ensure optimum continuity of service for critical functions
- Backup functionBackup function module - In conjunction with a battery pack, ensures continuity of service of a 24 V= system in the event of a power supply failure - Relay contacts and LED status indicators (normal operation, battery failed and battery discharged) - For mounting on a symmetrical rail depth 7.5 mm and 15 mm - Input voltage : 24 to 29 V= - Max. rating : 40 A - Width : 56 mm

Documentation

TECHNICAL DOCUMENTATION

-  [F02180EN-00.pdf](#) | PDF (0.34Mo)
-  [FT-F02180-FR-00.pdf](#) | PDF (0.7Mo)
-  [LE08163AA-01.pdf](#) | PDF (0.44Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0510.pdf](#) | PDF (0.03Mo)
-  [ex223001_0509.pdf](#) | PDF (0.03Mo)
-  [ex223001_0506.pdf](#) | PDF (0.08Mo)
-  [ex223001_0507.pdf](#) | PDF (0.06Mo)