

Product sheet



ATS LEGRAND

Automatic control switch control unit between two sources for DPX3 and DMX3 circuit breaker and CTX3 contactors

REF. 422682 | EAN. 3414970767813

> [Visit e-catalogue](#)

Product characteristics

- For advanced management of 2 breakers
- Interface LCD display, IR communication port on the Front panel for connection of USB or WiFi modules
- Power supply : 12 or 48 Vdc ; 100 - 240 Vac
- IP20
- Can be configured with the help of front panel touch keys or of the Legrand dedicated software

The product's benefits

Installation

- DPX3 platform has been developed to give a new solution of protection devices for a more precise approach in power installations in order to offer the correct answer for different project needs.

Usage

- DPX3 platform provide a complete "project" approach in premium market segment, offering a range completely suitable for high power application

Avantages

- DPX3 630 is the answer for the competition in the project sub-segment. A unique size for all versions (thermal magnetic, electronic with or without measure). Earth leakage fetures can be achieved by adding a dedicated module at the bottom of the breaker itself.

Documentation

TECHNICAL DOCUMENTATION

-  [LE09887AA.pdf](#) | PDF (4.63Mo)
-  [LE09863AA.pdf](#) | PDF (4.55Mo)
-  [LE09477AA_FR.pdf](#) | PDF (2.59Mo)
-  [LE09477AA_EN.pdf](#) | PDF (2.76Mo)
-  [EXB17039_GT_TransferSwitching.pdf](#) | PDF (17.73Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0223.pdf](#) | PDF (0.05Mo)
-  [ex223001_0222.pdf](#) | PDF (0.1Mo)

- LE09945AA_ver2.pdf | PDF (1.43Mo)
-  F02233FR_01_ATS_EVO_FRA.pdf | PDF (1.24Mo)
-  LE09480AA.pdf | PDF (3.65Mo)
- LE09129AC.pdf | PDF (8.85Mo)
- LE09511AA.pdf | PDF (3.41Mo)
-  LE09380AA.pdf | PDF (5.36Mo)
- F02233EN02_ATS_2_SOURCES_ENG.pdf | PDF (1.02Mo)
-  LE09877AA.pdf | PDF (3.79Mo)
- LE09507AA_EN.pdf | PDF (1.42Mo)

Software & configurators

-  Acu Configurator.zip | ZIP (99.82Mo)