

Product sheet



DPX³ -I 125 HP LEGRAND

DPX³-I 125HP trip-free switch, 4 poles 125A with earth leakage module

REF. 423187 | EAN. 3414971505452

DPX³-I 125 HP, trip-free switch for on-load circuit breaking and isolation of low voltage electrical circuits

> [Visit e-catalogue](#)

Description

DPX³-I 125 HP, trip-free switch for on-load circuit breaking and isolation of low voltage electrical circuits

Product characteristics

- According to EN/IEC standard 60947-3, suitable for commercial and middle power installations
- Rated insulation voltage of 500V - Rated impulse withstand voltage of 6kV
- Can be equipped with auxiliaries (undervoltage release, auxiliary contact), residual current relays, rotary handle, motor-driven handle, spreader, rear terminals and locking accessory
- Category of use AC 23A

Recommendation / Restriction

- Can be fitted with cage terminals 120mm² max. (flexible cable) or 150mm² max. rigid cable

Documentation

TECHNICAL DOCUMENTATION

 Workshop Book: DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.04Mo)

→ LE11962AB.pdf | PDF (2.46Mo)

 F03041EN01_DPX3125HP_TM RCD.pdf | PDF (2.52Mo)

 Cahier d'atelier : DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.32Mo)

 Technical Guide: Coordination between protection devices | PDF (5.41Mo)

Agreements & Certificates

The product's benefits

Installation

- Can be mounted on plate in Legrand cabinets and enclosures

Usage

- Climatic condition according to IEC/EN 60947-1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist

Avantages

- The most compact dimension of the market
- A range completely suitable for high power application with high performance breakers in compact dimensions

CATALOGUE PAGE & OTHERS

 ex223001_0186.pdf | PDF (0.09Mo)

 ex223001_0192.pdf | PDF (0.19Mo)

 ex223001_0194-0195.pdf | PDF (0.48Mo)

 ex223001_0190.pdf | PDF (0.16Mo)

 ex223001_0196-0197.pdf | PDF (0.52Mo)

 ex223001_0188.pdf | PDF (0.11Mo)



OC / CB-SE-104112 | (0.09Mo)