

# Product sheet



DPX³ -I 125 HP LEGRAND

DPX³-I 125HP trip-free switch, 3 poles 125A

REF. 423184 | EAN. 3414971505391

DPX³-I 125 HP, trip-free switch for on-load circuit breaking and isolation of low voltage electrical circuits

> [Visit e-catalogue](#)

## Description

DPX³-I 125 HP, trip-free switch for on-load circuit breaking and isolation of low voltage electrical circuits

### Product characteristics

- According to EN/IEC standard 60947-3, suitable for commercial and middle power installations
- Rated insulation voltage of 800V - Rated impulse withstand voltage of 8kV
- Can be equipped with auxiliaries ( undervoltage release, auxiliary contact), residual current relays, rotary handle, motor-driven handle, spreader, rear terminals and locking accessory
- Category of use AC 23A

### Recommendation / Restriction

- Can be fitted with cage terminals 120mm<sup>2</sup> max. (flexible cable) or 150mm<sup>2</sup> max. rigid cable

## Documentation

### TECHNICAL DOCUMENTATION

-  F03040EN01\_DPX3125HP\_TMv.1.0.pdf | PDF (3.18Mo)
-  Workshop Book: DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.04Mo)
-  LE11441AC.pdf | PDF (1.01Mo)
-  Cahier d'atelier : DPX³ 125HP/160HP/250HP/630/1600 | PDF (239.32Mo)
-  Technical Guide: Coordination between protection devices | PDF (5.41Mo)

### Agreements & Certificates

## The product's benefits

### Installation

- Can be mounted on plate in Legrand cabinets and enclosures

### Usage

- Climatic condition according to IEC/EN 60947-1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist

### Avantages

- A range completely suitable for high power application with high performance breakers in compact dimensions

### CATALOGUE PAGE & OTHERS

-  ex223001\_0186.pdf | PDF (0.09Mo)
-  ex223001\_0192.pdf | PDF (0.19Mo)
-  ex223001\_0194-0195.pdf | PDF (0.48Mo)
-  ex223001\_0190.pdf | PDF (0.16Mo)
-  ex223001\_0196-0197.pdf | PDF (0.52Mo)
-  ex223001\_0188.pdf | PDF (0.11Mo)



OC / CB-SE-104112 | (0.09Mo)