

Product sheet



LEGRAND

DCX-M changeover switche - size 6 - 3P - 1600 A - I-O-II

REF. 431113 | EAN. 3245064311137

> [Visit e-catalogue](#)

Product characteristics


- DCX - M changeover switches - from 40 to 1600 A - Conform to IEC EN 60947 - 3 - Moulded case design with frame parts of non-flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption - Knife - type contacts with self - wiping action on the contact surfaces, providing : - under heavy starting currents or with short - circuit conditions, the contact pressure is increased - shock and vibration proof contacts - Four breaking points per pole with two double - break contacts
- Changeover switches Size 6 - Connection with lugs - 3P - Intensity : 1600 A - Handle : I - O - II

Documentation


TECHNICAL DOCUMENTATION

→ 4207Z012_Y4514B.PDF | PDF (0.17Mo)

CAD & Design specs / BIM

 431113.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0242.pdf | PDF (0.12Mo)

 ex223001_0245.pdf | PDF (0.04Mo)