

Product sheet



LEGRAND

DCX-M changeover switch - size 3 - 3P+N - 400 A - I-O-II

REF. 431128 | EAN. 3245064311281

> [Visit e-catalogue](#)

Product characteristics

- DCX - M changeover switches - from 40 to 1600 A - Conform to IEC EN 60947 - 3 - Moulded case design with frame parts of non-flammable glass fibre reinforced polyester with high mechanical and electrical track resistance and with low water absorption - Knife - type contacts with self - wiping action on the contact surfaces, providing : - under heavy starting currents or with short - circuit conditions, the contact pressure is increased - shock and vibration proof contacts - Four breaking points per pole with two double - break contacts
- Changeover switches Size 3 - Connection with lugs - 3P+N - Intensity : 400 A - Handle : I - O - II

Documentation

TECHNICAL DOCUMENTATION

→ [4247Z007-Y4513A.pdf](#) | PDF (0.23Mo)

CAD & Design specs / BIM

 [431128.dwg](#) | DWG (0.12Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0242.pdf](#) | PDF (0.12Mo)

 [ex223001_0245.pdf](#) | PDF (0.04Mo)