

Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP44 - 200/250 V~ - 32 A - 3P+E

REF. 555255 | EAN. 3245065552553

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 44 - LV 16 and 32 A - sockets , plugs , mobile sockets , appliance inlets and interlocked switched sockets
Surface mounting sockets - Two possible angles (5° or 25°) 200/250 V~ - IP 44 32 A - 3P+E

Documentation

TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

-  555255.dwg | DWG (0.19Mo)
- Prises_non_verrouillées_saillies_200_250V.rfa | RFA (1.31Mo)
- surface_no_interlocked_sockets_200_250V.rfa | RFA (1.31Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0529.pdf | PDF (0.05Mo)
-  ex223001_0525.pdf | PDF (0.12Mo)
-  ex223001_0530.pdf | PDF (0.05Mo)
-  ex223001_0531.pdf | PDF (0.06Mo)

Agreements & Certificates

-  OC / CB-FR_710665 | (0.7Mo)
-  IMQ-CA02.05951 | (0.42Mo)
-  LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)