

Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 - IP66/67 - 380/415 V~ - 16 A - 3P+E

REF. 555358 | EAN. 3245065553581

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 66/67 LV 16 and 32 A Surface mounting sockets - Two possible angles (5° or 25°) 380/415 V~ - 16 A - 3P+E

Documentation

TECHNICAL DOCUMENTATION

-  F01811FR-02.pdf | PDF (3.67Mo)
-  F01811EN-03.pdf | PDF (9.37Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

-  555358.dwg | DWG (0.13Mo)
- Prises_non_verrouillées_saillies_380_415V.rfa | RFA (1.47Mo)
- surface_no_interlocked_sockets_380_415V.rfa | RFA (1.47Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0527.pdf | PDF (0.11Mo)
-  ex223001_0533.pdf | PDF (0.07Mo)
-  ex223001_0534.pdf | PDF (0.06Mo)

Agreements & Certificates

-  OC / CB-FR_710665 | (0.7Mo)
-  LGRP-2014-112-V1-EN.pdf | PDF (1.02Mo)
-  IMQ-CA02.05950 | (0.42Mo)