

Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 Pro - IP 66/67 - 380/415 V~ - 125 A - 3P+N+E

REF. 555659 | EAN. 3414970735133

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 66/67 LV 63 and 125 A Surface mounting sockets 380/415 V~ - 125 A - 3P+N+E

Documentation

TECHNICAL DOCUMENTATION

 F02385FR-01.pdf | PDF (2.98Mo)

 F02385EN-01.pdf | PDF (1.98Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

Prises_non_verrouillées_saillies_380_415V.rfa | RFA (1.47Mo)

 555659.dwg | DWG (0.13Mo)

surface_no_interlocked_sockets_380_415V.rfa | RFA (1.47Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0528.pdf | PDF (0.13Mo)

 ex223001_0534.pdf | PDF (0.06Mo)

 ex223001_0535.pdf | PDF (0.06Mo)

Agreements & Certificates

 LGRP-00201-V01.01-EN.pdf | PDF (0.71Mo)