

Product sheet



P 17 TEMPRA LEGRAND

Surface mounting socket P17 Pro - IP 66/67 - 380/415 V~ - 63 A - 3P+E

REF. 555558 | EAN. 3414970734921

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempa Pro IP 66/67 LV 63 and 125 A Surface mounting sockets 380/415 V~ - 63 A - 3P+E

Documentation

TECHNICAL DOCUMENTATION

 F02385FR-01.pdf | PDF (2.98Mo)

 F02385EN-01.pdf | PDF (1.98Mo)

 LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

 555558.dwg | DWG (0.18Mo)

Prises_non_verrouillées_saillies_380_415V.rfa | RFA (1.47Mo)

surface_no_interlocked_sockets_380_415V.rfa | RFA (1.47Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0528.pdf | PDF (0.13Mo)

 ex223001_0534.pdf | PDF (0.06Mo)

 ex223001_0535.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-FR_706516 | (1.27Mo)

 LGRP-00201-V01.01-EN.pdf | PDF (0.71Mo)