

Product sheet



P 17 TEMPRA LEGRAND

Mobile socket P17 Pro - IP 66/67 - 380/415 V~ - 63 A - 3P+E

REF. 555508 | EAN. 3414970734723

> [Visit e-catalogue](#)

Product characteristics

- P 17 Tempra Pro IP 66/67 LV 63 and 125 A Mobile sockets 380/415 V~ - 63 A - 3P+E

Documentation

TECHNICAL DOCUMENTATION

-  F02385FR-01.pdf | PDF (2.98Mo)
-  F02385EN-01.pdf | PDF (1.98Mo)
-  LE05815AA-01.pdf | PDF (2.53Mo)

CAD & Design specs / BIM

-  555508.dwg | DWG (0.2Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0528.pdf | PDF (0.13Mo)
-  ex223001_0534.pdf | PDF (0.06Mo)
-  ex223001_0535.pdf | PDF (0.06Mo)

Agreements & Certificates

-  OC / CB-FR_706516 | (1.27Mo)
-  LGRP-00206-V01.01-EN.pdf | PDF (0.71Mo)