

Product sheet



LINKEO LEGRAND

Linkeo 19 inches freestanding cabinet with single front and rear microperforated door capacity 42U
800x1200mm

REF. 446803 | EAN. 3414972027274

> [Visit e-catalogue](#)

Product characteristics

- Capacity 42U, dimensions (HxWxD) : 2052 x 800 x 1200mm
- Single Front and rear microperforated 80% door, which ensures a good air flow. Can be opened up to 220°. Equipped with 3 point lock mechanism and hinge system.
- Galvanised metal structure provides IP20 (protected against solid objects larger than 12.5 mm in diameter)
- Equipped with 4 x 19 inches uprights with U marking and adjustable depth
- Black RAL 9005

Recommendation / Restriction

- Maximum load carrying capacity : 1500kg (1000kg with levelling feet)

The product's benefits

Installation

- The whole structure stands on 4 levelling feet that can be adjusted from the floor. It can be completed with a set of 4 casters (ref. 446880) to ease the move of the cabinet. Cut-out at the top to install fan kit (ref. 446901, 446902, 446903 or 446904). Delivered ready-assembled.

Usage

- Pre-cut cable entries (top and bottom) to facilitate cable management. Equipped with 4 x 19 inches uprights with U marking and adjustable in depth.

Avantages

- Protected against solid objects larger than 12.5 mm (IP20), according to EN61587-1, IEC60529.

Documentation

TECHNICAL DOCUMENTATION

 F03351EN-00.pdf | PDF (2.63Mo)

 F03351FR-00.pdf | PDF (2.55Mo)

CAD & Design specs / BIM

Legrand_cabinet_Linkeo_DC_width_800.rfa | RFA (3.22Mo)

Legrand_baie_Linkeo_DC_largeur_800.rfa | RFA (3.22Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1031.pdf | PDF (0.11Mo)

 ex223001_1035.pdf | PDF (0.04Mo)

Agreements & Certificates

 LGRP-01457-V01.01-EN.PDF | PDF (1.04Mo)