

Product sheet



LEGRAND

French and German standard plate square version 2 modules - champagne

REF. 571582 | EAN. 3414971249141

> [Visit e-catalogue](#)

Product characteristics

- Arteur German and French standard plates - 60 mm fixing centres
- For 2 module mechanism - To be associated with surface mounting box Cat. No 5 723 90 or flush-mounting box Cat.No 0 800 41 and support frame Cat. No 5 760 20 (with claws) or 5 760 21 (with screws) - Square version - Neutral - Champagne

Documentation

TECHNICAL DOCUMENTATION

-  F03577EN-00.pdf | PDF (0.15Mo)
-  F03577FR-00.pdf | PDF (0.15Mo)

Agreements & Certificates

-  Decl. UE RED-A 4155 A | (0.45Mo)
-  OC / CB-FR_715034/M1 | (0.98Mo)
-  OC / CB-HU-005098 | (0.63Mo)
-  OC / CB-FR_705030/A1 | (1.68Mo)
-  Decl. UE RED-A 4133 A | (0.64Mo)
-  OC / CB-FR_709182/A1 | (0.66Mo)
-  OC / CB-DE 2-039435-M1 | (0.63Mo)
-  OC / CB-HU-005072 | (0.6Mo)
-  OC / CB-HU-005070 | (0.63Mo)
-  OC / CB-FR_717745 | (0.46Mo)
-  OC / CB-FR_717742 | (0.53Mo)
-  Decl. UE RED-A 4371 A | (0.43Mo)
-  Decl. UE RED-A 4048 C | (0.44Mo)
-  OC / CB-FR_705038/M1 | (2.34Mo)
-  Decl. UE RED-A 4166 A | (0.45Mo)
-  Decl. UE RED-A 4144 A | (0.45Mo)
-  Decl. UE RED-A 3812 B | (0.25Mo)
-  OC / CB-FR_707098 | (0.67Mo)

