

# Product sheet



## LEGRAND

### Cabinets PLEXO<sup>3</sup> - IP65 - IK09 - 4 rows - 18 modules

REF. 601838 | EAN. 3245066018386

> [Visit e-catalogue](#)

## Product characteristics

- Plexo<sup>3</sup> - IP 65 weatherproof cabinets, multifunction sleeves and Accessories - Self - extinguishing : resistance to incandescent wire 650°C. - Allows to achieve assemblies conform to IEC 61 439 - 3 - Weatherproof cabinets - IP 65 - IK 09 - Class II - Door and cabinet fully reversible. Removable chassis and faceplates from 2 - row versions up - 2 - position rail for modular products and moulded cases. Spacing between rails 150 mm - Can be fitted with perforated plates and solid faceplates for mounting non-modular products - Lockable door handle, sealable cover and faceplate - Shock - resistant polystyrene material - Box colour light grey L750A, cover colour dark grey R746A - Supplied without terminal blocks
- Cabinets 18 modules per row - Number of rows : 4

## Documentation

### TECHNICAL DOCUMENTATION

-  F01043FR-03.pdf | PDF (1.2Mo)
-  EXB22009\_Flipbook\_FR\_(03\_2022).pdf | PDF (6.2Mo)
-  EXB22026\_CA\_Plexo3\_FR\_imprimable.pdf | PDF (33.87Mo)
-  F01043EN-05.pdf | PDF (1.07Mo)
-  EXB14046\_CA\_Plexo3\_EN\_print.pdf | PDF (34.53Mo)
-  EXB22010\_Flipbook\_EN\_(03\_2022).pdf | PDF (6.56Mo)

### CAD & Design specs / BIM

- Legrand\_Cabinet\_Plexo<sup>3</sup>\_18\_modules.rfa | RFA (8.2Mo)
- Legrand\_Coffret\_Plexo<sup>3</sup>\_18\_modules.rfa | RFA (8.2Mo)

### CATALOGUE PAGE & OTHERS

-  ex223001\_0413.pdf | PDF (0.04Mo)
-  ex223001\_0412.pdf | PDF (0.11Mo)

### Agreements & Certificates

-  LOVAG-IT 17 .013-R02 | (1.1Mo)
-  OC / CB-654748 | (0.36Mo)
-  LGRP-00849-V01.01-EN.pdf | PDF (0.73Mo)