

# Product sheet



LCS<sup>3</sup> LEGRAND

LCS<sup>3</sup> 19" PDU 1U 12 x C13 IEC 60320 standard with 3m power supply cord

REF. 646815 | EAN. 3414970765383

PDU 19 inches 1U with 12 x C13 outlets with cord locking system, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

> [Visit e-catalogue](#)

## Description

PDU 19 inches 1U with 12 x C13 outlets with cord locking system, designed for supplying power to equipment in 19 inches enclosures. It comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

### Product characteristics

- Single phase
- 12 x C13 outlets with locking
- Input voltage 230V
- Input current 16A
- Maximum power 3.7kW

### Recommendation / Restriction

- Conforms to standard IEC 60320-2-2

## The product's benefits

### Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

### Usage

- Cord locking system : the cord is locked mechanically into the outlet to prevent any unintended disconnection (caused by maintenance, vibrations, etc.). This universal solution is compatible with all standard cords available on the market.

### Advantages

- Angle of outlets is 90°

## Documentation

### TECHNICAL DOCUMENTATION

 S000093176EN-15.pdf | PDF (3.09Mo)

 S000093176FR-15.pdf | PDF (3.1Mo)

### Agreements & Certificates

 LGRP-01739-V01.01-FR.pdf | PDF (0.91Mo)

 LGRP-01739-V01.01-EN.pdf | PDF (0.95Mo)

### CATALOGUE PAGE & OTHERS

 ex223001\_1015.pdf | PDF (0.13Mo)