

Product sheet



LEGRAND

Halogen free blue cable duct 25x40

REF. 636201 | EAN. 3245066362014

> [Visit e-catalogue](#)

Product characteristics

- Cable duct's cross - section : 25x40, 720mm² wiring capacity
- Grey color is for standard electrical circuits in installations.
- Hand - splitting cable duct thanks to the side and bottom cut - outs : no dust or rough edge when cutting to length.
- Halogen free product, does not release halogenated gases in case of fire.

Recommendation / Restriction

- Recommended for installations in buildings receiving public, rolling stock (e.g. : train, subway, etc.) or IT room.

The product's benefits

Installation

- The retaining bossage keeps the wires and cables at the bottom of the cable duct and prevents them from being pulled out during wiring. It also allows to wire on 2 levels. Those products allow a T-junction between a vertical cable duct and a horizontal one without obstacle : the lateral part is torn off thanks to the beginning of rupture at the bottom of the cable duct.

Usage

- The cover is easily installed on the cable duct by frontal-clicking or by rotation. The opening is done without tools. The ribbings on the edges of the cable duct help to align the labels.


Documentation

TECHNICAL DOCUMENTATION

 F02998EN-00.pdf | PDF (2.42Mo)

 F02998FR-00.pdf | PDF (2.41Mo)


Agreements & Certificates

 UL recogn-E212478 | (0.09Mo)

 NF Conduits-641237C | (0.18Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0481.pdf | PDF (0.18Mo)

 ex223001_0479.pdf | PDF (0.07Mo)