

Product sheet



LINKEO LEGRAND

Linkeo plinth for cabinets width 800 mm x depth 1000 mm

REF. 646404 | EAN. 3245066464046

> [Visit e-catalogue](#)

Product characteristics

- Height 100mm
- Plinth fixed using M12 screws. Traps fixed using zinc - plated M6 screws.
- Corner blocks made of 2 mm thick steel + paint (same as cabinets)
- Traps 1.5 mm thick steel + paint with double fold reinforcement on floor side
- Color : charcoal grey RAL 7016 (same as the cabinets)

Recommendation / Restriction

- Useful to raise the cabinet, so that the cables can be fed into the entry from below, particularly when there is no raised floor. It can be used to store extra length of cable, or route the cables through 2 linked cabinets. Also, it protects the cabinet base from dirt and humidity.

The product's benefits

Installation

- Supplied with complete set of screws for the equipotential link with the cabinet. Can be fixed to the floor (screws not supplied).

Usage

- Possibility to place 2 plinths one on top of the other.

Advantages

- Uniformity of the structure : the plinths are the same colour as the cabinets

Documentation

TECHNICAL DOCUMENTATION

- LE09826AA-02.pdf | PDF (1.38Mo)
- 📄 F02420EN-01.pdf | PDF (2.28Mo)
- 📄 F02421FR-01.pdf | PDF (2.29Mo)
- LE09825AA-03.pdf | PDF (1.09Mo)
- 📄 F02420FR-01.pdf | PDF (2.28Mo)

CATALOGUE PAGE & OTHERS

- 📖 ex223001_0944.pdf | PDF (0.14Mo)
- 📖 ex223001_0943.pdf | PDF (0.07Mo)