

Product sheet



LINKEO LEGRAND

Wall-mounting cabinet 10 inches 6U 300mm depth

REF. 646230 | EAN. 3414970967947

[> Visit e-catalogue](#)

Product characteristics

- Equipped with fix side panel
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking.
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

Recommendation / Restriction

- For indoor use only

The product's benefits

Installation

- Delivered ready-assembled

Usage

- Thanks to its integrated lock, it can be used in any space

Avantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

Documentation

TECHNICAL DOCUMENTATION

→ [LE10110AA-01.PDF](#) | PDF (1.8Mo)

 [F02825EN-00.pdf](#) | PDF (0.38Mo)

 [F02825FR-00.pdf](#) | PDF (0.38Mo)

Agreements & Certificates

 [LGRP-01458-V01.01-FR.pdf](#) | PDF (0.73Mo)

 [LGRP-01458-V01.01-EN.PDF](#) | PDF (1.24Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0945.pdf](#) | PDF (0.09Mo)