

# Product sheet



LINKEO LEGRAND

Wall-mounting cabinet 10 inches 6U 300mm depth

REF. 646230 | EAN. 3414970967947

> [Visit e-catalogue](#)

## Product characteristics

- Equipped with fix side panel
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking.
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

## Recommendation / Restriction

- For indoor use only

## The product's benefits

### Installation

- Delivered ready-assembled

### Usage

- Thanks to its integrated lock, it can be used in any space

### Advantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

## Documentation

### TECHNICAL DOCUMENTATION

→ LE10110AA-01.PDF | PDF (1.8Mo)

F02825EN-00.pdf | PDF (0.38Mo)

F02825FR-00.pdf | PDF (0.38Mo)

### Agreements & Certificates

LGRP-01458-V01.01-FR.pdf | PDF (0.73Mo)

LGRP-01458-V01.01-EN.PDF | PDF (1.24Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_0945.pdf | PDF (0.09Mo)