

# Product sheet



## LINKEO LEGRAND

Wall-mounting cabinet 19 inches 15U 600mm width  
450mm depth - delivered flatpack

REF. 646253 | EAN. 3414970968043

> [Visit e-catalogue](#)

## Product characteristics

- Equipped with removable side panel.
- Supplied with 2x19 inches up Rights adjustable in depth and with U marking. Set of 2 optionnal up Rights to install at the rear of the cabinet ref 646243
- Reversible flat safety glass door with screen - printing and integrated lock
- 3 pre-cut cable entries (top, bottom and rear). Perforations for natural ventilation. Can also house fan kit ref 646238
- Anthracite grey RAL 7016

## Recommendation / Restriction

- For indoor use only

## The product's benefits

### Installation

- Side panels can be removed to access easily inside the cabinet for cabling

### Usage

- Thanks to its integrated lock, it can be used in any space

### Advantages

- Continuity of the cabinet metal conductive parts is achieved by design
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

## Documentation

### TECHNICAL DOCUMENTATION

→ LE10111AA-02.pdf | PDF (7.52Mo)

F02826EN-00.pdf | PDF (0.6Mo)

F02826FR-00.pdf | PDF (0.6Mo)

### CAD & Design specs / BIM

Fix\_wallmount\_cabinets\_Legrand\_Linkeo\_with\_removable\_side\_panel.rfa | RFA (1.89Mo)

Legrand\_Linkeo\_coffrets\_fixes\_avec\_panneaux\_lateraux\_amovibles.rfa

### CATALOGUE PAGE & OTHERS

ex223001\_0945.pdf | PDF (0.09Mo)

### Agreements & Certificates

LGRP-01458-V01.01-FR.pdf | PDF (0.73Mo)

LGRP-01458-V01.01-EN.PDF | PDF (1.24Mo)

| RFA (3.74Mo)