

Product sheet



LEGRAND

Emergency luminaire B65 - standard maintained / non maintained - 100 lm - 1h - LED

REF. 661431 | EAN. 3414970311917

> [Visit e-catalogue](#)

Product characteristics

- B65 LED - weatherproof self - contained emergency lighting luminaire LED - Weatherproof LED maintained and non-maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs. IP 65 - IK 07 - Plug - in base to ease Fixing , cabling and connection - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours - Charge monitor with a green LED. Power supply : 230 V $\pm$ 10% - 50/60 Hz. Class II - High - capacity screw terminals (2 x 2.5mm²) - 3 flexible cable entries for 16, 20 and 25 mm tubes - Can be equipped with metallic protection grids Cat.Nos 0 626 90/92
- Standard luminaires - Maintained/non-maintained (M/NM) - Standard luminaires require normal lighting manual switching off in order to test emergency lighting - These Maintained luminaires can also operate in non-maintained mode according to the wiring of normal lighting - 100 lm - 1h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

 S000083090EN-3.pdf | PDF (3.47Mo)

 S000083090FR-3.pdf | PDF (3.67Mo)

 LE06963AF.pdf | PDF (0.46Mo)

CAD & Design specs / BIM

Legrand_Emergencia_B65LED_EN.rfa | RFA (0.51Mo)

CATALOGUE PAGE & OTHERS

 Legrand 661431 B65LED 100LM-1H M.zip | ZIP

 ex223001_0911.pdf | PDF (0.05Mo)

Agreements & Certificates

 AENOR S-007/000004 | (0.91Mo)

 ENEC-ENEC/000993 | (0.46Mo)