

# Product sheet



MOSAIC™ LEGRAND

IP44 floor box for tile from 18 to 24mm

REF. 689622 | EAN. 3245066896229

> [Visit e-catalogue](#)

## Product characteristics

- To be installed in back box Ref. 0 896 04
- No cable exit. Requires removal of the cover during use.
- Removable plain cover
- For tile thickness from 18 to 24 mm
- To be equipped with 1 kit of vertical supports Ref. 6 896 57 for Arteur/Mosaic mechanism

## Recommendation / Restriction

- For installation in concrete floor only - Temperature of use, transport and storage: -5° à +60°

## The product's benefits

### Installation

- Provide a minimum height from 86 to 114mm maximum including 65 to 90 mm of concrete.

### Usage

- Cleaning: do not use abrasive products or detergents.

### Advantages

- Can be used as access trap. Floor box with one kit of vertical supports Ref. 6 896 57 for Arteur/Mosaic mechanism
- Allows the installation of different thicknesses of tiles and other coatings

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE06000AA-04.pdf](#) | PDF (2.53Mo)

 [F02080EN-04.pdf](#) | PDF (1.22Mo)

 [F02080FR-04.pdf](#) | PDF (1.28Mo)

### CAD & Design specs / BIM

[Legrand-ip44-floor-boxes-EN.rfa](#) | RFA (1.02Mo)

[Legrand-boites-de-sol-ip44-FR.rfa](#) | RFA (1.02Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_1162.pdf](#) | PDF (0.06Mo)

 [ex223001\\_1161.pdf](#) | PDF (0.11Mo)